


Catalyst Testing Plant



- **Heated convection oven flushed with inert gas**
 - 3 zone split furnace with tubular reactor
- **Feed dosing with high pressure HPLC pump**
- **Industrial control system**

Technical Data

Dimension plant W x D x H	1680 mm x 800 mm x 1920 mm
Mass of the unit without computer + spares	500 kg
Electrical supply	3 x N/PE 230/400V AC, 50 Hz, 16A, 6 kW,
Ambient conditions	10 to 40 °C, max. humidity < 85 %
Pressure conditions	-1 to 200 bar @ temperatures up to 350 °C
Temperature conditions	-10 to 350 °C under pressure, -10 to 550 °C pressureless
Convection oven	2 kW, 148 °C
Vertical split furnace	3 zones, design temperature 1000 °C
Reactor type	Tubular stainless steel reactor, DN 15
Gas supplies	Nitrogen, low pressure: 2-3 bar, high pressure: 160 bar Hydrogen, 160 bar Air, 6 bar
Liquid supplies	Viscous or solid hydrocarbons with melting temperature < 130 °C
Gas / liquid separation	Cyclone with differential pressure sensor for liquid level measuring



Product Overview



Smart Solutions for Small Plants

AP-Miniplant GmbH & Co. KG
Hirtenrasen 64
D-37318 Lindewerra

Phone: +49 (0) 36087 976-0
Fax: +49 (0) 36087 976-22

Email: info@miniplant.de
Internet: www.miniplant.de